

## LVS-9580

Durable, portable handheld verifier—



Weighs only 16.7 oz. (.47 kg)

## Portable Barcode Verification System

The LVS-9580 is a high-performance handheld solution for off-line barcode verification to ISO/IEC, ANSI, GS1, and UDI standards. Featuring a high-resolution 5.0 megapixel camera, the LVS-9580 reads and analyzes linear (1D) and two-dimensional (2D) codes up to 3.0 inches (76.19 mm) wide and up to 2.25 inches (57.15 mm) tall. 1D and 2D direct part marks (DPM) of up to 1.75" x 1.75" (44 mm x 44 mm) can be verified to MIL-STD-130, ISO, and GS1 standards.

The LVS-9580 verifies multiple symbologies, including any combination of linear, 2D (Data Matrix, QR Code, and Aztec Code), and stacked linear (PDF417, MicroPDF, and Composite codes).

Powered by a 10-foot (3.0 m) USB 2.0 cable, the LVS-9580 verifies barcodes on a wide range of surfaces including plastics, PCBs, metal, cardboard, and shipping containers.

### LVS-9580: At a Glance

- Stitching feature to grade barcodes larger than the field of view.
- Ideal for multiple line production and warehouse environments.
- Validates printed barcodes to ISO/IEC, ANSI, GS1, and UDI print quality standards.
- Validates direct part marks (DPM) to ISO, MIL-STD-130, and GS1 standards.
- Software upgrade options include Multi-Sector for verification of multiple barcodes on a label.
- 21 CFR Part 11 compliant-ready.
- Supports 15 languages with the ability to add more.
- Quality data reporting for auditing purposes.
- Includes NIST-Traceable Calibrated Conformance Standard Test Card for calibrating the system.

For more information, visit [www.microscan.com](http://www.microscan.com).

### LVS-9580: Available Symbologies

	Standard 	Postal 		
Linear				
	Data Matrix 	QR Code 	Micro QR Code 	Aztec 
2D				
	Micro PDF417 	PDF417 	GS1 DataBar 	
Stacked				

Please see the second page for a complete list of supported symbologies.

#### ISO/ANSI for 1D

LVS-95XX series barcode verifiers inspect all nine ISO and ANSI parameters for linear (1D) barcodes, have the ability to identify blemishes, and can perform simple human-readable validation.

#### ISO/ANSI for 2D

The LVS-95XX series verifies 2D codes and reports all parameters as specified in the applicable symbology specification.

#### Analytical Tools

Equipped with numerous analytical tools to identify and evaluate barcode errors. Problems are color-coded to make problem solving easy.

#### Software

LVS-95XX software includes GS1 System Symbol Specification Tables. GS1 tables set standards for barcode data structure and how to maintain the quality of codes during barcode creation. Microscan offers an online training course on GS1 tables and how these apply to different organizations.

#### Software Upgrade: EAIV

The Enhanced Application Identifier Verification (EAIV) option verifies that all GS1 Application Identifiers, such as Expiration Date, Global Trade Item Number (GTIN), and Batch Number, embedded in the data structure of a GS1 barcode match the data programmed in the EAIV feature by the user.

#### User Permission Options

Manage permissions through LVS-95XX software: Passwords are stored in a local database. All passwords are encrypted, include an expiration date, and count failed password attempts.

Manage permissions through Microsoft Active Directory: User privileges are based on Microsoft authentication and LVS-95XX permissions are assigned based on group membership.

#### Portability

Connects to the latest tablets.

#### Field of View

- 3.0" (76 mm) horizontal
- 2.25" (57.15 mm) vertical
- DPM: 1.75" (44 mm) x 1.75" (44 mm)

# MICROSCAN®

# LVS-9580 SPECIFICATIONS AND OPTIONS

## SUPPORTED STANDARDS

### Application Standards

AIAG/DAMA/JAPIA/Odette  
ALDI  
ISO/IEC TR 29158 (DPM Cat 0, 1, 2)  
DHL  
FPMJ  
French CIP  
GS1 General Specifications  
HDMA Guidelines  
Health Industry Barcode (HIBC)  
IFAH  
Italian Pharmacode  
Japan Codabar  
Laetus Pharmacode  
Laetus Standard  
MIL-STD-130N  
Pharmacy Product Number (PPN)  
Automatic GS1 or ISO  
GS1 (NTIN)  
Miniature Pharmacode  
Postal (EIB, USPS IMB/Code 128, POSTNET, Japan Post)  
PZN-big, normal, small (German Pharmacode)

### GS1 US Certification

Data Matrix for Healthcare  
Data Matrix (ECC 200)  
EAN/UPC  
EAN/UPC and extended codes  
EAN/UPC with CC  
GS1 DataBar Omnidirectional  
ITF-14  
GS1 DataBar-14 with CC (formerly RSS-14 with CC)  
UCC/EAN with Supplementals  
UCC/EAN-128  
UCC/EAN-128 with CC

### ISO Conformance Standards

ISO/IEC 15415, 15416  
ISO/IEC 15426-1, 15426-2  
ISO/IEC TR 29158 (DPM Cat 0)  
All supported ISO/IEC Symbology Specifications

## MECHANICAL

**Height:** 215.9 mm (8.5")  
**Width:** 120.6 mm (4.75")  
**Depth:** 139.7 mm (5.5")  
**Weight:** Unpackaged weight: .47 kg (16.7 oz.)  
Shipping weight (includes all cables and other items packaged in shipping box): approx. 1.81kg (4 lbs.)

## FIELD OF VIEW

**Standard:** 76.19 mm (3.0") horizontal  
57.15 mm (2.25") vertical  
**DPM:** 44 mm (1.75") x 44 mm (1.75")

## MINIMUM BAR CODE X-DIMENSION

1D = 4.0 mils (0.10 mm)  
2D = 5.9 mils (0.15 mm)

## MINIMUM PC REQUIREMENTS

PC supplied by customer.  
Windows® 7 Professional, Windows® 8.1 Pro, or Windows® 10 Pro;  
Intel® Core™ i3 or higher;  
4 GB RAM;  
800 x 600 Screen Resolution;  
One USB 2.0 port available per unit.

## SUPPORTED SYMBOLOGIES

### Linear (1D) Symbologies

Codabar  
Code 128, Code 39, Code 93  
DataBar  
DataBar Expanded and Limited  
DataBar Omnidirectional  
DataBar Stacked and Truncated  
EAN/JAN-13  
EAN/JAN-8  
Enterprise Intelligent Barcode (EIB)  
4-State (4SB)  
GS1-128  
Hanxin Code  
HIBC  
Interleaved 2 of 5 (ITF)  
ITF-14  
Japan Post  
MSI Plessey  
Pharmacode-Italian and Laetus  
PZN 7 and PZN 8  
UPC-A and UPC-E  
USPS-128  
USPS Intelligent Mail Barcode (4-State Customer Barcode)

### Two-Dimensional (2D) Symbologies

Aztec  
DataBar with CC-A, CC-B, or CC-C  
EAN/JAN-13 with CC-A, CC-B, or CC-C  
EAN/JAN-8 with CC-A, CC-B, or CC-C  
ECC-200 (Data Matrix) including:  
• EIB CMDM  
• French CIP  
• GS1 Data Matrix  
• NTIN and PPN  
GS1-128 with CC-A, CC-B, or CC-C  
MaxiCode  
Micro QR Code  
MicroPDF417  
PDF417  
QR Code  
UPC-A with CC-A, CC-B, or CC-C  
UPC-E with CC-A, CC-B, or CC-C  
Note: CC = Composite Components  
Contact Microscan for a complete list of supported ECC-200 (Data Matrix) codes.

## ILLUMINATION

Type: Red filter (660nm)

## ELECTRICAL

USB powered 5 VDC @ 180 mA

## COMMUNICATIONS

USB 2.0 A plug to Mini-B plug cable  
3 m (10 ft.)

## CAMERA

5.0 megapixel camera  
Object Distance: Contact

## ENVIRONMENTAL

Operating Temperature: 4° to 46° C  
(40° to 115° F)  
Relative Humidity: 5% to 95%  
(no water condensation allowed)

## 21 CFR PART 11

The LVS-9580 is certified by GS1 US and is 21 CFR Part 11 compliant-ready.

## CALIBRATION

EAN/UPC Calibrated Conformance Test Card (included with system)

## SAFETY CERTIFICATIONS DESIGNED FOR

FCC, CE, UL

## RoHS COMPLIANT

## QMS CERTIFICATION

[www.microscan.com/quality](http://www.microscan.com/quality)

©2017 Microscan Systems, Inc. SP098C-EN-0217

Warranty – For current warranty information about this product, please visit [www.microscan.com/warranty](http://www.microscan.com/warranty).



**MICROSCAN®**  
[www.microscan.com](http://www.microscan.com)